

Lifta Solus 6000



DIMENSIONS

+ Chair width	621 mm
+ Seat width	458 mm
+ Footrest width	295 mm
+ Distance manual seat to footrest	470 mm
+ Distance electric seat to footrest*	525 mm
+ Rail diameter	45 mm
+ Distance folded chair to wall*	405 mm
+ Distance unfolded chair to wall*	679 mm

PERFORMANCE

+ Load	up to ca. 135kg
+ Speed	ca 0.12m/second
+ Engine power	0.26kW

OPERATION

- + Ergonomically shaped operating lever with integral on/off key switch (either right or left armrest)
- + Wireless remote control
- + Manual swivel seat (electric seat optional)

RAIL GUIDES

- + Customised steel double-rail system (powder-coated)
- + Wall mounting possible (optional)
- + Automatic folding rails optional

PROPULSION

- + Sealed electrical motor with rechargeable battery
- + Charging station at bottom and top of stairs
- + Control shaft laterally behind the guide rail

ELECTRICAL CONNECTION

- + 230V alternating current
- + Socket required at top/bottom end of the rail

SAFETY

- + Type-tested safety device
- + Speed limiter
- + Automatic end switch
- + Integral safety sensors in the footrest and drive unit
- + Self-locking gearbox and braking device
- + The lift stops automatically when the controls are released
- + Seat with integral weight sensor (from 35kg)
- + Safety belt



* The dimensions may vary for construction purposes depending on local installation conditions. | Update 03/2016

Lifta Stairlifts SA (Pty) Ltd
Unit No 13A St. Michaels Park,
Corner St. Michaels Road &
Howe Street, Observatory,
Cape Town 7925